

Angle sensor
(plastic / conductive)
4166500010



Supply	5 ± 0.1 V	Return spring	No
Angle range	86°	Voltage range	680 mV – 4,250 mV
Absolute linearity	± 2.5 %	Temperature range	- 40 °C to + 125 °C
Resistance	4.1 kΩ ± 20 %	Life time full stroke	Min. 2 mio. cycles
Dither life time (± 2°)	Min. 20 mio. cycles	Connector	Female connector on request