

Pressure sensor 96705



Media	Liquid media e.g. fuel, hydraulic oil	Pressure range	To 0 + 2000 bar
Temperature range	- 40 °C to + 125 °C	Output signal	0 10 V, 0 5 V, 0 5 V, 1 5 V, 0.5 4.5 V, ratiometric
Thread	1/4 ", 1/2", metric	Connector	AMP timer, 3-polig, cable MVS/A, MVS/C, M12x1 (S763) and others Female connector on request