

Capacitive sensors DC

- 4-wire 20 mm body
- M12 connector type
- N / O & N / C complimentary
- ESD protected

| | | | |
|-----------------------------------|--------------------|----------------------------------|--------------------|
| PNP (complimentary) | CPU-010V-ETN | Wiring | 4-wire |
| NPN (complimentary) | CNU-010V-ETN | Rated operational voltage | 7 to 30 DC V |
| Mounting | unshielded | Rated operational current | 350 mA |
| Rated operating distance Sn | 10 mm | Utilisation category | DC 13 |
| Repeatability | ≤ 10 % | Impulse voltage withstand | 1 kV 1.2 / 50 μs V |
| Function indication | yes | Inrush current | 1.5 A |
| Ambient temperature range | -25 °C to +70 °C | Frequency of operating cycles | 10 Hz |
| Pollution degree | 3 | Minimum operational current | ≤ 0.01 mA |
| Time delay before availability | ≤ 22 ms | No-load supply current | ≤ 8 / 8 mA |
| Housing size | 20 mm | Off-state current | ≤ 100 μA |
| Housing material | PBT | Voltage drop | ≤ 1 V |
| Degree of protection | IP 67 | Short circuit protection | yes (pulsed) |
| Connection | 4pin M12 connector | Reverse polarity protection | yes |
| Current type | DC | | |

