

## **Temperature sensor**

94121



Connector		Dimensions	
	SW 27	M15x15-6g Ø25+0,1	59×1 5+0.1 11+0.3 2 10+0.1 0/246-0.2 0/246-0.2 0/246-0.2
Media	Liquid media e.g. water, oil, fuel	Thread	M16 x 1.5
Nominal resistance NTC	2,050 Ω (25 °C), 186 Ω (100 °C) *	Connector	DIN Bajonett (DIN 72585), Female connector on request
Nominal resistance PTC	1000 Ω (0°C)	Protection range	IP 6K6K / 6K7 / 6K8 / 6K9K
Temperature range	- 40 °C to + 155 °C	Order number	9412100900
Time of response	T90 < 15 s (water)		