



Inductive proximity sensor

- M8 stainless steel housing
- 2m cable
- PNP / normally closed

Item code	IPC-002-ADN / 3	Circuit protection	surge, overload, short-circuit and verse polarity protection
Sensing distance	2 mm	Indicator	yellow LED
Mounting	non-flushed	Ambient temperature	-25 ... 70 °C
Output	PNP NC	Ambient moisture	35 ... 95 % RH
Supply voltage	10 ... 30 VDC	Switch frequency	1500 Hz
Standard target	Fe 8*8*1t	Voltage resistant	1000 V / AC 50 / 60 Hz 60 s
Switch shifts	≤ ± 10 %	Insulation resistant	≥ 50 MΩ (500 VDC)
Hysteresis	1 ... 20 %	Vibration withstand	repeated amplitude 1.5 mm 10 ... 50 Hz (2 hours each for X, Y, Z direction)
Repeated error	≤ 3 %	Protection	IP 67
Load current	≤ 150 mA	Housing material	stainless steel
Residual	≤ 2.5 VDC	Connection	2 m cable
Current consumption	≤ 10 mA		



BN:+ BK: out BU: -